

# RJN 系列软胶囊机

Rjn series soft capsule machine

## 产品介绍:

软胶囊机可将油类液体、混悬液或糊状物定量注入胶膜中，形成大小、形状、色彩各异的密封软胶囊。由于软胶囊具有崩解速度快、生物利用率高、外形雅致、易于吞服、不易氧化、便于贮存和携带等优点，越来越受到消费者的欢迎。软胶囊机由于生产率高、装量准确、质量稳定、成品率高而越来越受到厂家的青睐，现已广泛用于医药、保健品、化妆品和游戏彩弹等领域。


软胶封装系统由主封装机以及输送装置、熔胶罐、配料罐、冷水机、定型转笼干燥机、电气控制面板、带小车的烘箱托盘、储罐等组成。

Softgel encapsulation machine can quantitatively inject the oil, mixing suspension and pasty mass into the capsule to form all kinds of softgel encapsulation with different size, shape and color. Because of the merits of high speed disintegration, easy to oral, hard to oxygenation, easy to store and take, the softgel encapsulation is welcomed by more and more customers. Owing to the high productivity, charging exactly, quality stabilization, high finished product rate, it is favoured by more and more manufacturers and used in the fields of medicine, health products, cosmetic and game-color ball and so on.

The softgel encapsulating system consists of main encapsulation machine as a crucial apparatus and conveyer, gelatin melting tank, dosage tank, water chilling unit, tumble dryer for formalization, electrical control panel, oven tray with dolly, storage tank, etc.



## 软胶丸工艺流程 Workflow of Soft Gelatin Capsule



### 技术参数 Main Technical Parameter

| 型号项目 ITEM  | RJN-115   | RJN-200              | RJN-300              |
|--|---|----------------------|----------------------|
| 液模转速<br>Rotary speed of die roll                           | 0-4rpm  | 0-5rpm               | 0-5rpm               |
|  | 变频无级调速 Frequency conversion stepless speed regulation |                      |                      |
| 最大产量<br>Max Capacity                                       | 12800pcs/h  | 65000pcs/h           | 110000pcs/h          |
| 流体单柱塞供给量<br>Supplying Volume for flow single-pillar pistol | 0-1ml   | 0-2ml                | 0-2ml                |
| 装量差异<br>Difference among filling volume                    | ± 2%  | ± 2%                 | ± 2%                 |
| 整机功率<br>Power for whole machine                            | 4KW   | 7.5KW                | 17.6kw               |
| 外形尺寸<br>Contour sizes                                      | 600 × 850 × 1650mm                                    | 1500 × 1150 × 2000mm | 2420 × 1180 × 2210mm |
| 整机重量<br>Weight of whole machine                            | 650Kg   | 1050Kg               | 1900Kg               |

## 扬州诺亚机械有限公司 YANGZHOU NUOYA MACHINERY CO.,LTD

诺亚一厂地址: 中国江苏扬州市邗江区杨寿镇工业区二期华通南路2-11号  
No.1 Factory Address: No.2-11, Huatong South Road, phase II,  
yangshouzhen Industrial Zone, Hanjiang District,  
Yangzhou, Jiangsu Province, China

诺亚二厂地址: 扬州仪征刘集镇盘古工业区创业路58号  
No.2 Factory Address: 58 Chuangye Road, Pangu Industrial Zone, Liuji,  
Yizheng, Yangzhou

诺亚三厂地址: 扬州仪征市刘集镇六巷村马庄组11号  
No.3 Factory Address: No. 11, Mazhuang group, Liuxiang village,  
Liuji Town, Yizheng City, Yangzhou

电话 (TEL) : 86-514-87667808, 87667998  
手机 (Mobile) : 0086-13813182501  
邮编 (Zip code) : 225000  
网址 (Web) : www.noah-pm.com  
邮箱 (Email) : noah@noah-pm.com  
352580121@qq.com

## 深圳市诺亚制药设备有限公司 SHENZHEN NUOYA PHARMACEUTICAL EQUIPMENT CO.,LTD

地址: 中国深圳宝安区观澜创新工业园B栋  
ADD: No. B of Chuangxin Industry Area, Guanlan, Baoan District  
Shenzhen Guangdong China

电话 (Tel) : 86-755-27600661  
手机 (Mobile) : 0086-13813196394  
邮编 (Zip code) : 518110  
网址 (Web) : www.noah-equipment.com  
邮箱 (Email) : sznoah@noah-pm.com 2885283049@qq.com

